

ACL-600 SERIES

The ACL-600 Series is a wireless, portable jump light simulator kit for mock door training. The standard ACL kit contains one Controller and two or more Light Modules, all powered by one CR123 battery.

Each kit is coded with a unique network ID to prevent interference with other ACL systems in use nearby.

Optional handheld training alarm bell, (ATB-1), is also available for simulated training.

TYPICAL OPERATION

- Attach the Light Module(s) to the training door frame with line-of-sight visibility to trainees.
- Turn the modules ON by pressing the black pushbutton switch at the top of each device.
- The BLUE indicator illuminates on all active modules. If the BLUE indicator does not illuminate on any device, replace the battery.
- Test and confirm that the RED, AMBER, and GREEN lights illuminate when the corresponding colored pushbuttons on the Controller are pressed.
- Confirm that YELLOW and GREEN lights will not illuminate unless RED is illuminated first..
- Immediately prior to training, turn Light Modules ON, but turn Controller OFF (all lights OFF).
- When training starts turn Controller ON, and press RED button (RED light ON). Press AMBER or GREEN lights ON per training SOP.
- After training, turn all devices OFF by the black pushbutton at the top of each module Confirm all lights and BLUE indicators are OFF. Stow properly.





STANDARD KITS

- ACL-602 (One Controller, Two Light Modules)
- ACL-604 (One Controller, Four Light Modules)
- ACL-607 (One Controller, Seven Light Modules)

ACCESSORY

• ATB-1 - Airborne Training Bell

